



**Part Number :** [2070190008](#)  
**Product Description :** Mini-Fit Sigma Sealed Cap for 8 Circuit Plug Housing  
**Series Number :** 207019  
**Status :** Active  
**Product Category :** Connector Accessories



---

## Documents & Resources

### Drawings

[Drawing 2070190008\\_sd.pdf](#)  
[Packaging Design Drawing 2070180000-PK-000.pdf](#)

### 3D Models and Design Files

[3D Model 2070190008\\_stp.zip](#)

### Specifications

[Application Specification 2070170000-AS-000.pdf](#)  
[Product Specification 2070170000-PS-000.pdf](#)  
[Test Summary 2070170001-TS-000.pdf](#)  
[Test Summary 2070170000-TS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

### [Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

### [Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Connector Accessories
Series	207019
Description	Mini-Fit Sigma Sealed Cap for 8 Circuit Plug Housing
Component Type	Cap
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma Sealed
UPC	193264428571

### Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Thermoplastic Elastomer
Net Weight	7.200/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

### Use with Part(s)

Description	Part Number
Mini-Fit Sigma Sealed Plug Housing, Dual Row, 4.20mm Pitch, 8 Circuits, UL94V-0, Natural	<u>2070170008</u>

---

---

This document was generated on Sep 26, 2024