


SHEET 1 OF 1




CONTACT CONFIGURATION
TIMING (BBM) NON-SHORTING










NOTE:
1. ALL DIMENSIONS IN MM[INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
   X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
▲4. CONTACT MATERIAL: GOLD FLASH
5. CONTACT RATING: 150MILLIAMP, 250VAC/DC
   350MILLIAMP, 110VAC/DC
6. CONTACT RATING (NON-SWITCHING) 5A
7. OPERATING FORCE 800 ± 300gf-cm
8. OPERATING TEMP: -30°C to 85°C
▲9. CIRCUIT SP: 5 POSITION 30° INDEX.
10. DIELECTRIC STRENGTH: 1000V RMS MIN.@ SEA LEVEL
▲11. HARDWARE SUPPLIED ON SWITCH:
   STOP RING, LOCKWASHER and HEXNUT
12. ▲ DENOTES CRITICAL PARAMETER.



RECOMMENDED PCB LAYOUT

REV	ECO NO	DESCRIPTION	DATE	BY
C	ECO-101206	print update	08/29/22	MW

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

OBJECT ID 000012507

TITLE KC15A9.501NPF

SCALE	DATE	DR	DWG	REV
3:2	9/1/2004	AR	G510602	C

Downloaded from Arrow.com.