

## SEK CAB FLAT COLOR AWG28/7 10P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 010 7005
Specification	SEK CAB FLAT COLOR AWG28/7 10P 30,48m
HARTING eCatalogue	<a href="https://b2b.harting.com/09180107005">https://b2b.harting.com/09180107005</a>

### Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

### Version

Cable length	30.48 m
Number of cores	10
Core structure	AWG 28/7

### Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Impedance	100 Ω
Conductor resistance @ 20 °C	≤216 Ω/km
Insulation resistance @ 20 °C	≥20 MΩ x km

### Material properties

Material (cable)	PVC
Colour (cable)	Colour coded
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance

## Material properties

REACH Annex XVII substances	No
-----------------------------	----

REACH ANNEX XIV substances	No
----------------------------	----

REACH SVHC substances	No
-----------------------	----

## Commercial data

Packaging size	1
----------------	---

Net weight	790 g
------------	-------

Country of origin	Germany
-------------------	---------

European customs tariff number	85444993
--------------------------------	----------

eCl@ss	27061801 Data and communication cable (copper)
--------	--