



Part Number : [1301530120](#)

Product Description : Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA 5-20, 20A, 120V, 1.83m (6.0') Cord Length

Series Number : 130153

Status : Active

Product Category : Power Distribution

Engineering Number : 20051-6A



Documents & Resources

Drawings

[1301530120_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Automatic Reset, NEMA 5-20, 20A, 120V, 1.83m (6.0') Cord Length
Enclosure Rating	NEMA 4X
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678888283

Agency

UL	E66308
----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Automatic
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	125V

Physical

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	1.83m (6.0')
Cord Type	12/3 SJE00W
Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon

Mounting Style	Portable
Number of Receptacles	1
Packaging Type	Bag
Receptacle Type	N/A

This document was generated on Sep 24, 2025