



Part Number : [08701030](#)

Product Description : SPOX Crimp Terminal, 24-18

AWG, Brass, Bag

Series Number : 5194

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 5194TL

Packaging Alternative : [08701031](#) (Reel)



Documents and Resources

Drawings

[008701030_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[51949200-200.pdf](#)

[PS-5096-003-001.pdf](#)

[PS-5195-001-001.pdf](#)

[PS-5195-002-001.pdf](#)

[PS-5195-005-001.pdf](#)

[PS-5195-009-001.pdf](#)

[PS-5195-010-001.pdf](#)

[PS-5195-011-001.pdf](#)

[PS-5196-001-001.pdf](#)

[PS-5196-004-001.pdf](#)

[PS-5196-005-001.pdf](#)

[PS-5196-006-001.pdf](#)

[PS-5197-001-001.pdf](#)

[PS-5197-003-001.pdf](#)

[PS-5197-004-001.pdf](#)

[PS-5273-003-001.pdf](#)

[PS-5273-004-001.pdf](#)


Tooling Specifications

[CS-5194-001.pdf](#)

[CS-5194\(S\)-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5194
Description	SPOX Crimp Terminal, 24-18

	AWG, Brass, Bag
Application	Signal
Product Name	SPOX
UPC	800753745834

Agency

CSA	LR19980
-----	---------

Electrical

Current - Maximum per Contact	7.0A
-------------------------------	------

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	185.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.20mm
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
SPOX 3.96mm Pitch Single Row Receptacle Housings	<u>5195</u>
SPOX 5.08mm Pitch Single Row Receptacle Housings	<u>5197</u>
SPOX 5.08mm Pitch Single Row Receptacle Housings	<u>5198</u>

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for SPOX Terminals, 24-18 AWG	<u>638116500</u>
Extraction and Activation Tool	<u>638132700</u>

Japan

Description	Part Number
Hand Crimp Tool JHTR5904	<u>11260058</u>
Hand Extraction Tool	<u>11260100</u>

This document was generated on May 09, 2026