



Catching Your Eyes !

Language

[About](#) | [News](#) | [Product](#) | [Technology](#) | [Contact us](#) | [Exhibition](#) | [Investor](#) | [Hu](#)

PR

2.2 inch LTPS TFT LCD Module

Model No. TD022SREC2

Mobile Phone

- DSC
- Mobile Phone
- PDA/Pocket PC
- Automotive Display
- Notebook PC

Less contacts and components High system integration High brightness,



Features

- High contrast ratio
- High brightness
- High pixel density
- High color saturation
- Low power consumption
- RGB I/F

Applications

- Mobile Phone, Smart Phone

SPECIFICATIONS

ITEM	DESCRIPTION
Display Size (Diagonal)	2.2 inch
Display Type	Transflective
Active Area (HxV)	33.84 x 45.12mm
Number of Dots (HxV)	240 x RGB x 320 dot
Dot Pitch (HxV)	0.047 x 0.141mm
Color Arrangement	RGB Stripe
Color Numbers	65k / 262k
Surface Treatment	Hard Coating
Luminance (B/L On)	150cd/m ²
Contrast	100:1
Viewing Angle (B/L On)	U/D: 100° L/R: 110°
Operation Temperature	-20~70℃J
Storage Temperature	-30~80℃J
Sample Schedule	Ready

Production Schedule

Ready

[Home](#) | [Site Map](#) | [Contact Us](#)

Copyright © 2003 Toppoly Optoelectronics Corp. All Rights Reserved.
