



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	SIGNAL											E2	
		E1	1	2	3	4	5	6	7	8	9	10		11
51939-293_- NOTE 3	D C B A		U	U	U	U	U	U	U	U	U	U	U	
			T	T	T	T	T	T	T	T	T	T	T	
			S	S	S	S	S	S	S	S	S	S	S	
			R	R	R	R	R	R	R	R	R	R	R	
			U	U	U	U	U	U	U	U	U	U		



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
U	[6.86]	SIGNAL
T	[6.86]	SIGNAL
S	[6.86]	SIGNAL
R	[6.86]	SIGNAL

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date			linear	0.X ±0.3	COPY		www.fciconnect.com	
A	DG07-0184	JMG	05/07/07				0.XX ±0.13	projection		title 44S	
						angles	0.XXX ±0.051			RIGHT ANGLE STB HEADER	
						dr	0° ±2°			product family PwrBlade	
						enrg	JM GUO 05/07/07	scale		code 213	
						chr	RYAN YUAN 05/07/07			size dwg no	
						appd	GARY HSIEH 05/07/07			A 51939-293	
							JOSEPH HSIA 05/07/07			sheet 1 of 4	
sheet index	revision sheet	A	A	A	A						
		1	2	3	4						


cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51939-293--
NOTE: 3



BROKEN-OUT SECTION A-A
SCALE 2:1



SECTION C-C



PARTIAL SECTION E-E

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date					COPY		www.fciconnect.com	
A				linear		0.X ±0.3		projection		title 44S	
						0.XX ±0.13				RIGHT ANGLE STB HEADER	
				angles		0.XXX ±0.051				product family PwrBlade	
				dr	JM GUO	05/07/07				code 213	
				enr	RYAN YUAN	05/07/07				size dwg no	
				chr	GARY HSIEH	05/07/07				sheet 2 of 4	
				appd	JOSEPH HSIA	05/07/07				51939-293	
sheet index	revision sheet							scale 1:1		A	
										cage code 22526	

Pro/E

3

cage code 22526


4

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51939-293--
NOTE: 3



RECOMMENDED PCB LAYOUT

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear		0.X ±0.3		COPY		www.fciconnect.com	
A						0.XX ±0.13		projection		title 44S	
						0.XXX ±0.051				RIGHT ANGLE STB HEADER	
				angles		0° ±2°				product family PwrBlade	
				dr	JM GUO	05/07/07		scale		code 213	
				enr	RYAN YUAN	05/07/07		size		sheet 3 of 4	
				chr	GARY HSIEH	05/07/07		A		dwg no 51939-293	
				appd	JOSEPH HSIA	05/07/07		1:1		cage code 22526	
sheet index	revision sheet										

Pro/E

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

B

4

4

3

22526

4