

1-925369-2 Product Details

Share Print Email



Active
View 3D PDF

.100 AMPMODU Headers, Housings & Contacts

MOD 4 REC.HSG 1X12P
1-925369-2
TE Internal Number: 1-925369-2

Product Highlights View All

- Connector
- Housing
- Connector Style = Receptacle
- Contact Type = Socket
- 2.54 mm Centerline

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Feedback

Documents Features Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Connector
Connector Type	Housing
Mating Connector Lock	Without
Connector Series	Mod IV
Keyed	No

Termination Features	
Termination Method to Wire/Cable	Crimp

Body Features	
Row-to-Row Spacing (mm [in])	2.54 [0.100]

Contact Features	
Contact Type	Socket

Housing Features	
Connector Style	Receptacle
Centerline (mm [in])	2.54 [0.100]
Mating Alignment	Without
Housing Color	Green
Housing Material	Nylon - GF

Configuration Features	
Number of Positions	12
Number of Rows	1
Strain Relief	With
Housing Configuration	Both Ends Closed

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Flammability Rating	UL 94-HB

Other	
Brand	AMP

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy
- Global Accessibility Statement

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

