© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

CONNECTOR HOUSINGS



✔ Active

TE CONNECTIVITY (TE)

AMP LATTICE 28P PLUG HSG

LATTICE PRODUCTS | LATTICE

176763-1
TE Internal Number: 176763-1

EU RoHS Compliant
EU ELV Compliant

Number of Positions 28

Housing Material Nylon

Connector Style Plug

Sealable No

Operating Temperature Range (°C) -20 – 105

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

AMP LATTICE CONN. PLUG HOUSING 28 POS

PDF **(TIFF AVAILABLE)**

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Downloaded from Arrow.com.

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

Product Specifications

Application Specification

Crimping Of AMP Lattice Contact

TIF

English

Crimping Of AMP Lattice Contact

PDF

English

Product Specification

AMP Lattice Connector

TIF

Japanese

AMP Lattice Connector

PDF

Japanese

Qualification Test Report

AMP Lattice Connector

PDF

English

AMP Lattice Connector

TIF

English

Agency Approvals

Agency Approval Document

AMP LATTICE CONNECTOR REPORT

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Plug
Sealable No
Product Type Housing

Downloaded from Arrow.com.

Configuration Features

Number of Positions 28

Electrical Characteristics

Operating Voltage (VAC) 250

Body Features

Material Nylon
Color Gray

Housing Features

Housing Material Nylon
Housing Color Gray

Dimensions

Length (mm) 33.5
Width (mm) 21.3

Usage Conditions

Operating Temperature Range (°C) -20 – 105

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Method Bag
Packaging Quantity 200

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.