Part Number : 1731110362
Product Description : FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 2, Straight or 90° Angle Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws
Series Number : 173111
Status : Active
Product Category : D-Sub Backshells
Engineering Part Number : FPHGR-2A



Documents and Resources

Drawings

1731110362_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026) SCIP:6814239a-6f3b-49e5-9b10-026c607c5649
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	173111
Description	FCT Plastic Backshell for D-Sub Connector, Shielded, Shell Size 2, Straight or 90° Angle Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws
Magnetic	Yes
Product Name	FCT Products
Type	Plastic
UPC	191128458511

Electrical

Shielded	Yes
Shield Type	Shielded Plastic

Physical

Cable Diameter	max. 8.00mm
Material - Backshell	PC+ABS
Material - Screw	Steel
Mounting Style	Locking Screw
Net Weight	16.700/g
Orientation	Straight or 90° Angle
Packaging Type	Carton

Downloaded from Arrow.com.

Plating - Backshell	Nickel
Shell Size	2
Temperature Range - Operating	-35° to +95°C
Thread Size	4-40 UNC
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 2

Downloaded from Arrow.com.