



**Catalog No. TC140**

**Description:** SADDLE SPRT MTG BASE .5X.4IN NAT NY

**UPC No** 5414363058199

**Home > Wire & Cable Management > Ty-Rap > Cable tie mounts**

Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 14.29mm (0.563 Inches), Width of 8.73mm (0.344 Inches), Height of 6.75mm (0.266 Inches), Mount with #4 Screw, Bulk Pack

**Descriptors**

Category	Cable tie mounts
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Application	Used for wire bundles, cables, and hoses to panels

**Specifications**

Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Screw
Operating Temperature	-40 to +185 F

**Classifications**

Brand Name	Ty-Rap
------------	--------

**Dimensions**

Mount Size	#4
------------	----

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant

ETIM	EC000449 Mounting base and -element for cable ties
Length	14.29 mm
Length	0.56 inch
Width	8.73 mm
Width	0.34 inch
Height	6.75 mm
Height	0.27 inch

**by ABB**

ETIM	EC000449 Mounting base and -element for cable ties
Type of fastening	Other
Material	Plastic
Material quality	Polyamide (PA)
Colour	Natural colour

**Certification/Standard**

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	ZODZ	N/A	N/A