





Printed on 7 Nov 2023 14:26 (China Standard Time) from M4032745




B

A



PN 2351051-2/-4 AS SHOW
UNLESS SPECIFIED DIMENSION
ARE SAME WITH 2351051-1

Printed on 7 Nov 2023 14:26 (China Standard Time) from M4032745




KOZ LEGEND	
	ZONE 1: BACKPLATE ZONE, NO OTHER COMPONENT PLACEMENT ALLOWED, 0.0MM HEIGHT RESTRICTION
	ZONE 2: SECONDARY SIDE SOCKET CAVITY ZONE, 2.25MM MAX COMPONENT HEIGHT.

REFERENCE BACKPLATE KEEPOUT ZONE

FOR GENERAL BOARD DESIGN, PLEASE REFER TO THE THERMAL AND MECHANICAL DESIGN GUIDELINES PROVIDED BY INTEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JEFF WANG 05AUG2019	 TE Connectivity				
		CHK BILL LV 05AUG2019					
DIMENSIONS: mm	 0 P/LC ±0.3 1 P/LC ±0.3 2 P/LC ±0.3 3 P/LC ±0.3 4 P/LC ±0.3 ANGLES ±3° FINISH	APVD SIMON LI 05AUG2019	NAME LGA4677-1 SOCKET SOCKET E1 BACKPLATE ASSY	SIZE A1	CAGE CODE 00779	DRAWING NO C=2351051	RESTRICTED TO -
		PRODUCT SPEC 108-115173					
		APPLICATION SPEC 114-115032					
		WEIGHT					
MATERIAL		CUSTOMER DRAWING		SCALE 2:1	SHEET 3	OF 4	REV A1



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JEFF WANG 05AUG2019	TE Connectivity	
		CHK: BILL LV 05AUG2019		
DIMENSIONS: mm		APVD: SIMON LI 05AUG2019	NAME: LGA4677-1 SOCKET	
		PRODUCT SPEC	SOCKET E1 BACKPLATE ASSY	
		108-115173	SIZE: CAGE CODE: DRAWING NO:	
		APPLICATION SPEC	RESTRICTED TO:	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ±0.3	114-115032	
		1 PLC ±0.3	WEIGHT: -	
MATERIAL	FINISH	2 PLC ±0.3	CUSTOMER DRAWING	
		3 PLC ±0.3	SCALE: 2:1	
ANGLES	±	4 PLC ±	SHEET 4 OF 4	
		±3	REV A1	

printed on 7 Nov 2023 14:26 (China Standard Time) from M4032745