

Pressing tool PZ 1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Type	PZ 1.5
Order No.	9005990000
Version	Pressing tool, Crimping tool for wire-end ferrules, 0.14mm², 1.5mm², Trapezoidal crimp
GTIN (EAN)	4008 190085964
Qty.	1 pc(s).

Creation date November 11, 2020 5:26:23 AM CET

Catalogue status 06.11.2020 / We reserve the right to make technical changes.

Pressing tool

PZ 1.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Width	170 mm	Width (inches)	6.693 inch
Weight	170 g	Net weight	171.171 g

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Description of contact

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, min.	0.14 mm ²
Crimping range, max.	1.5 mm ²	Conductor cross-section, max. AWG	AWG 16
Conductor cross-section, min. AWG	AWG 26		

tool data crimping

Crimping type/profile	Trapezoidal crimp	Wire end ferrules cross-section, min.	0.25 mm ²
Wire end ferrules cross-section, max.	1.5 mm ²		

Classifications

ETIM 6.0	EC000168	ETIM 7.0	EC000168
eClass 9.0	21-04-38-11	eClass 9.1	21-04-38-11
eClass 10.0	21-04-38-11	UNSPSC	31-16-31-02

Approvals

Approvals



Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN CAT 2 PORTFOLIOGUIDE EN
Engineering Data	WSCAD
User Documentation	Manual

Pressing tool PZ 1.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

