




Rev	AWO #	Description	Date	Appr
-		RELEASED	9/10/13	

APPROVED: _____
DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:
Insulator: PA66, rated UL 94V-0
Insulator color: Green
Screw: Steel, M3.0/Zinc plated
Cage: Brass, Nickel plated
Pin Header: Brass, Tin plated

Electrical:
Voltage rated: 300 VAC
Current rated: 16 Amps
Contact resistance: 20 mΩ
Insulation resistance: 500 MΩ @ 500 VDC
Withstanding voltage: 2000V AC/1 Min

Mechanical:
Solid wire: 26-12AWG 2.5mm²
Torque (Lb-in): 0.5Nm (4.5lb-in)
Strip length: 6-7mm
Temperature Rating:
Operating temperature: -40°C to +105°C
Environmental:
Lead free, RoHS compliant.



Positions: 02 thru 24
A = .200 [5.08] x No. of Positions
B = .200 [5.08] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES EXCEPT AS NOTED

INCHES
.X ± .10
.XX ± .020
.XXX ± .015
HOLE
ØX ± .10
ØXX ± .015
ØXXX ± .010

TITLE

ADAM TECH
909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

EURO BLOCK, .200 [5.08] PITCH

APPROVALS	DATE	SIZE	PART NO.	REV.
DRAWN AY	7/9/14	X	EB147A-XX-D	-
CHECKED SY	7/9/14			
APPROVED		REF: S00067C	SCALE: NTS	SHEET 1 OF 1