

Han-Port Rahmen 1-fach, sw, Metalldeckel



Image is for illustration purposes only. Please refer to product description.

Part number	39 50 000 0120
Specification	Han-Port Rahmen 1-fach, sw, Metalldeckel
HARTING eCatalogue	https://harting.com/39500000120

Identification

Category	Sockets
Series of hoods/housings	Han-Port®
Element	Frames
Specification	Single
	Metal version, CPD black
	Metal cover, CPD black

Technical characteristics

Limiting temperature	-10 ... +60 °C
Storage temperature	-25 ... +60 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Smoothed surface
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Net weight	311 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140154773
eCl@ss	27182810 Cover/infill panel/identification strip (electrical cabinet)
ETIM	EC002617
UNSPSC 24.0	39121321