


REV.	DATE	DESCRIPTION
NC	10/31/01	INITIAL RELEASE



DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	APPROVALS		DATE	 connex Connector Corporation TITLE N JACK TO MCX JACK ADAPTOR			
1 BODY	BRASS	NICKEL		DRAWN	G.R.S.	10/31/01				
2 INSULATOR	TEFLON	NATURAL		CHECKED			SIZE FSOM NO. DWG. NO. REV.			
3 CONTACT PIN	BER COPPER	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	ISSUED						
4							SCALE NA PART NO. 242172 SHEET 1 OF 1			
5										
6							SIZE FSOM NO. DWG. NO. REV.			
7										
8			DO NOT SCALE DRAWING							