








B



- NOTES:
1. PLUG KIT CONSISTS OF:
PRE-INSERTED PLUG BODY & SHIELD
MANAGEMENT BAR ASSEMBLY
FERRULE
GROMMET
 2. MATERIALS:
PLUG BODY: CLEAR POLYCARBONATE, UL94 V-0
MANAGEMENT BAR: BLACK POLYCARBONATE, UL94 V-0
CHANNEL COMPENSATOR: NICKEL PLATED BRASS
SHIELD: TIN PLATED BRASS
CONTACTS: COPPER ALLOY, SELECTIVE GOLD PLATING
FERRULE: NICKEL OR TIN PLATED BRASS
GROMMET: POLYCARBONATE, UL94 V-0, COLOR: BLACK
 3. CONTACTS TERMINATE SOLID OR STRANDED CONDUCTORS UP TO .037 [0.94] OUTSIDE DIAMETER OF INSULATION.
 4. FOR PRODUCT SPECIFICATION, SEE PR026-01.
 5. DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD.
 6. TERMINATED PLUG HEIGHT: .237 [6.02] ±.005 [0.13] ON CABLE.
 7. DESIGNED FOR CATEGORY 6 APPLICATIONS.



A



RoHS



BULK	50 MICRO-INCHES [1.27um]	SS-39200-006
PACKAGE	CONTACT PLATING IN MATING AREA	PART NUMBER

THIRD ANGLE PROJECTION						11118 Susquehanna Trail South Glen Rock, PA 17327-9199 (717) 235-7512 http://www.stewartconnector.com			
		8 x 8 CATEGORY 6 SHIELDED PLUG ASSEMBLY WITH MANAGEMENT BAR, FERRULE & GROMMET							
DO NOT SCALE DRAWING									
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE									
DIMENSIONS: INCHES [METRIC]		THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://BELFUSE.COM/STEWART/STEWART-PATENTS/				DRN BY:		DATE	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE $\pm .005$ [0.13] ANGLES ARE $\pm 1^\circ$						JAM		5-21-01	
						APPD BY:		DATE	
SHEET NO.						TRM		5-22-01	
						DWG. NO.		REV.	
1 OF 1						CT390009		A7	

B

A