

1

2

3





4

A

B


C

Copyright FCI



DA3W3P300A30LF
DA3W3P300A40LF
PART NUMBER

LAYOUT DIMENSIONS (after plating)
CONNECTOR SIDE VIEW



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8639-0001

European Views

rev	ecn no	dr	date
A	LS05-0106	MPE	2005/11/22
B	LS06-0095	LGO	2006/06/17
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	PESSON	2005/11/22	ANGULAR	LINEAR	size
Eng	PESSON	2005/11/22			1.5
Chr	LEGARE	2005/11/22	0.XX* $\pm 2^{\circ}$	0.XXX ± 0.1	ECN
Appr	LEGARE	2005/11/22	Product family	D-SUB	Spec ref
FCI		PIN CONNECTOR SUB D WITH POWERS CONTACTS			Rev.
					dwg no
					C01-8639-2297
					B
					CUSTOMER sheet 1 of 1

REV F - 2006-04-17

PDM: Rev:B

STATUS Released

Printed: Oct 01, 2010