



2250068-2

- DESCRIPTION
- SUPPORT
- REQUEST QUOTE
- DOCUMENTS

1X1 726 10/100 TAB UP WITHOUT LED

Tech Help

Brand	TRP
Number of Ports	1X1
Speed	10/100BASE-T
LED	No
LED Type	-
Height Profile	Standard
Port Configuration	Tab Up
Operating Temperature	0 to 70°C
EMI Tabs	Yes
PoE Rating	N/A

RECOMMENDED PRODUCTS



L898-1A4T-43
[1xN Port MagJack® ICM](#)
[See Details](#)



L836-1X1T-47
[1xN Port MagJack® ICM](#)
[See Details](#)



SI-60114-F
[1xN Port MagJack® ICM](#)
[See Details](#)

Products

- Cable Assemblies
- Circuit Protection
- Connectors
- Linear Transformers
- Magnetic Solutions
- Power Solutions
- See All

Bel Groups

- Bel Fuse-Circuit Protection
- Bel Magnetic Solutions
- Bel Power Solutions
- Cinch Connectivity Solutions
- Signal Transformer
- Stewart Connector
- TRP Connector

Information

- Contact Us
- Privacy Statement

Connect with Us



Explore Bel

- About Us
- Bel Extranet
- Careers
- Investors
- News Room

Copyright © 2017, Bel Fuse Inc. All Rights Reserved.

