

Johanson Part Number 4700BP14A0600001T

Johanson Part Number: 4700BP14A0600001T

Johanson Company: JTI

Legacy P/N: 4700BP14A0600T

Size for Capacitors (EIA): None

Description: Band Pass Filters, 603, 4400-5000MHz, 3W, 2.5dB, Ni/Sn (RoHS), 4.7GHz Band Pass Filter, EIA 0603, SMD, Low Loss and High Attenuation, 7" Reel Paper Tape

Specification Number: None

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.016

Schedule B: 8534.00.00.85

Thickness (Min): None

ITAR: No

End Band(Min): 0.01

ECCN: EAR99

End Band (max): 0.012

RoHS Compliance: Yes, RoHS 10/10

Standard Item: No

REACH: Yes

Lead Time Typical (Weeks)*: 16

Country of Origin: TW

Length (Min): 0.057

Product Family: Integrated Passive Components

Length (Max): 0.069

Product Subfamily: Band Pass Filters

Width (Min): 0.025

Capacitance Value: None

Width (Max): 0.037

Cap Unit of Meas: None

Part Weight (mg): None

Tolerance: None

Packaged Width (lb) Arm: None

Voltage: None

Packaging: 7" Reel Paper Tape

Dielectric Temp Coefficient: None

Packaging Qty: 4000

Termination: 0

Operating Temp Range: -40°C to +85°C

Marking: Special

Storage Temp Range (Packaged): -40°C to +85°C

Product Release Date: Oct. 21, 2019, 7 a.m.

Storage Temp Range (None Operating): +5°C to +35°C with RH 45% to 75%

Harmonization: 8534.00.00.85

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://johansontechnology.com/band-pass-filters>

Printed from: www.johansontechnology.com/search/pn-detail/4700BP14A0600001T/