

VB RJ45 LaR -VB RJ45 LaR FRNC grey 7.5m




Image is for illustration purposes only. Please refer to product description.

Part number	09 48 858 5585 075
Specification	VB RJ45 LaR -VB RJ45 LaR FRNC grey 7.5m
HARTING eCatalogue	https://b2b.harting.com/09488585585075

Identification

Category	System cabling
Series	RJ45
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING VarioBoot RJ45 Preferred directions left/right
Connector 2	HARTING VarioBoot RJ45 Preferred directions left/right
Type of cable	Copper cable (round)
Description of the cable	Wiring 1:1 Flame retardant Halogen-free

Version

Cable length	7.5 m
Number of cores	8
Core structure	4x 2x AWG 26/7

Technical characteristics

Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-20 ... +60 °C unmoved
	0 ... +60 °C moved
Degree of protection acc. to IEC 60529	IP20
Minimum bending radius	10x Cable diameter (singular bending)
	5x Cable diameter (repeated bending)

Material properties

Material (cable)	FRNC (LSZH)
Colour (cable)	Grey

Specifications and approvals

Specifications	ISO/IEC 11801
	IEC 61156-6
	IEC 60332-1 Flame retardancy
	IEC 60754-2 Halogen freeness
	IEC 60754-2 Non corrosive
	IEC 61034 Low smoke

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140250291
eCl@ss	27060308 Patch cord copper (data cable)