



Johanson Product Information for 500F14N220KT4T

Johanson Company: Johanson Dielectrics inc.

Product Release Date: 28 March, 2014

Deprecated P/N: 500F14N220KT4T

Web Page Link:

<https://www.johansondielectrics.com/emi-chip-filter/feedthru-mlcc>

Datasheet Date: 01-06-2024

Description: Capacitors Feed-thru, 0603, NP0/C0G, 50V, 22pF±10%, Ni/SnPb, 7" Reel Paper Tape

Size for Capacitors (EIA): 0603

Thickness (Max): 0.026

Life Cycle Stage: Last buy (with effective Last Order Date)

Thickness (Min): 0.000

Schedule B: 8532

End Band (Min):

ECCN: EAR99

End Band (Max):

RoHS Compliance: No

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes. 11

Country of Origin: US

Product Family: Capacitors

Length (Min): 0.059

Product Subfamily: Capacitors Feed-thru (Obsol.)

Length (Max): 0.069

Capacitance Value: 22.000

Width (Min): 0.030

Cap Unit of Meas: pF

Width (Max): 0.040

Tolerance: ±10%

Packaged Weight (lb) Arm: 0.00

Voltage: 50.0

Packaging: 7" Reel Paper Tape

Dielectric Temp Coefficient: NP0/C0G

Packaging Qty: 4000

Termination: 6

Operating Temp Range: -55°C to +125°C

Marking: No Mark

Storage Temp Range (Packaged): -65°C to +125°C

Storage Temp Range (Non Operating): +5°C to +40°C with RH 20% to 70%