



Part Number : [191930245](#)

Product Description : VersaKrimp Ring Tongue Terminal for 6 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Carton

Series Number : 19193

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : E-360-10



Documents and Resources

Drawings

[191930245 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 6 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755050912

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	4.840/g
Packaging Type	Carton
Stud Size	10 (M5)

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	9.10mm max.
Wire Size (AWG)	6
Wire Size mm ²	16.00

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900004</u>
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	<u>192940008</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Square "DIN" style dies for 6 AWG	<u>640037770</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640074300</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>

This document was generated on Jun 02, 2026