



Part Number : 191930230

Product Description : VersaKrimp Ring Tongue Terminal for 6 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton

Series Number : 19193

Status : Planned for Obsolescence


Product Category : Ring and Spade Terminals

Engineering Number : E-358-38

Documents & Resources

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS |  |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2024)4144-DC (27 June 2024) |
| EU RoHS | Compliant per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|----------|--------------------------|
| Status | Planned for Obsolescence |
| Category | Ring and Spade Terminals |

| | |
|----------------|---|
| Series | 19193 |
| Description | VersaKrimp Ring Tongue Terminal for 6 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton |
| Keyword | Ring Terminal, Ring Terminals |
| Product Family | VersaKrimp Terminals and Splices |
| Product Name | VersaKrimp |
| Type | Ring |
| UPC | 800755050783 |

Agency

| | |
|-----|---------|
| CSA | LR18689 |
| UL | E32244 |

Physical

| | |
|-----------------------------|----------------------|
| Barrel Type | Closed - Brazed |
| Insulation | None |
| Material - Plating Mating | Tin |
| Net Weight | 7.530/g |
| Packaging Type | Carton |
| Stud Size | 3/8" (M9) |
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter | 9.09mm max. |
| Wire Size (AWG) | 6 |
| Wire Size mm ² | 16.00 |

Application Tooling

Global

| Description | Part Number |
|---|------------------|
| Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices | <u>192860117</u> |
| Die Set (Large) for the HHLS Hydraulic Crimper | <u>192900004</u> |
| PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals | <u>640013900</u> |

| | |
|---|------------------|
| Square "DIN" style dies for 6 AWG | <u>640037770</u> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <u>640074300</u> |
| Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices | <u>638162000</u> |

This document was generated on Jul 29, 2024