

Part Number : [457503112](#)

Product Description : Mini-Fit Plus Female Crimp Terminal, 16 AWG, Copper Alloy, Tin (Sn) Plating, Bag

Series Number : 45750

Status : Active

Product Category : Crimp Terminals

Packaging Alternative : [457503111](#) (Reel)



Documents and Resources

Drawings

[457503112_sd.pdf](#)

[PK-5556-003-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


Specifications

[55560002-AS-000.pdf](#)

[PS-45750-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	45750
Description	Mini-Fit Plus Female Crimp Terminal, 16 AWG, Copper Alloy, Tin (Sn) Plating, Bag
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. See Molex product specification PS-45750-001 for additional current de-rating information. Series 45750 is Hot-Swappable
Product Name	Mini-Fit Plus
UPC	822350286046

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	100
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.50mm
Wire Size (AWG)	16
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit TPA Dual Row Receptacle Housings	<u>30067</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>42474</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>43760</u>
Mini-Fit BMI Dual Row Receptacle Housings	<u>44516</u>
Mini-Fit Jr. Receptacle Housings	<u>5557</u>
Mini-Fit Jr. Dual Row Receptacle Housings	<u>46992</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	<u>11030044</u>
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	<u>2002182200</u>

This document was generated on Apr 24, 2026