

 [Live Product Chat](#)



Product Highlights:

- Switch - Mechanical
- DPS8 Series
- Code Type = 2 position
- Termination Type = PC Tails
- Mount = Rear

[View all Features](#) | [Find Similar Products](#)

TE Part Number: 2-1437603-3

✓ Active

 Add to Part List

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Product Drawings:

- [Outline Drawing Code Switch Dual Pushbutton \(DPS8 Se...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Switch - Mechanical
- Code Type = 2 position
- Termination Type = PC Tails
- Mount = Rear
- Configuration (Pole-Throw) = Single Pole - Double Throw

Electrical Characteristics:

- Contact Rating = 0.4 VA max @ 20 VDC or peak AC

Body Related Features:

- Series = DPS8
- Mount Style = Snap Detent

Configuration Related Features:

- Wheel Markings = + & -
- Repeating Readout = With

Industry Standards:

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Other:

- Brand = Alcoswitch