

YA1CLBOX, Comp. Term., Cu, Standard, 1-Hole

By Burndy
Catalog # [YA1CLBOX](#)



Copper Compression Terminal, Standard Barrel, 1 AWG, 1-Hole, 5/16" Stud, Tin Plated, UL/CSA

Features

- Barrel designed with internal chamfer at wire entry for smooth insertion of wire, preventing possible damage of the strands
- Standard barrel length is recommended for installations with limited space availability
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL 486A-486B
Buy America(n) Qualified	<ul style="list-style-type: none"> • Buy America Compliant (All status valid till December 2025) • Buy American Act Compliant (All status valid till December 2025) • BABA Compliant (All status valid till December 2025)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1 AWG
Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	75 (37) Navy
Conductor Size	1 AWG
Conductor - Copper Str Size Range	1 AWG
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	1
Connector Type	STANDARD BARREL

Current

Voltage - Maximum	35000
Voltage Rating	35 kV

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.46 in
Dimension - L Length Overall mm	49 mm
Dimension - Pad Width inch	0.68 in
Package Height	0.000 in
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - Strip Length inch	15/16
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16
Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	Straight
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.34 in

General

Die Index	11
Trade Name	HYLUG™
Sub Brand	HYLUG
Color Code	Green
Physical Attribute - Tongue Type	Standard
Plated	Y

Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Type	Standard Barrel, Tin Plated
UPC 12 Digit	781810551257
UPC 14 Digit GTIN	00781810551257
Material	COPPER
Plating Type	Electro-Tin plated
Finish Type	Tin-Plated

UPC 781810551257

Logistics

Minimum Pack Quantity	1
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-YA1CLBOX-SPEC-EN | REV 4/2026