

REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

NOTES:

Insulator Material: PBT, UL 94V-0

Contact Plating: Flash Gold

Contact Material: Brass



Current Rating : 1A AC,DC

Contact Resistance: 20MΩ Max.

Dielectric Withstanding: AC 500V

Insulator Resistance: 1000MΩ Min.

Operating Temp.: -40°C~+105°C



NUMBER OF POSITIONS	DIMENSION		
	A	B	C
10	32.00	10.16	27.94
14	34.54	12.70	33.02
16	39.62	17.78	35.56
20	44.60	22.86	39.70
24	49.78	27.94	45.72
26	52.32	30.48	48.26
30	57.40	35.56	53.34
34	62.48	40.64	58.42
40	70.10	48.26	66.04
50	82.80	60.96	78.74
60	95.50	73.66	91.44
64	100.58	78.74	96.72

UNLESS TOLERANCE		DRAW	BY	CnC Tech,LLC Part NO. 3010-XX-002-12-00			
GENERAL	ANGLE	DESIGN	BY				
X. ± 0.30	X.° ± 3.0°	CHECK	BY				
.XX ± 0.20	.X° ± 2.0°						
.XX ± 0.15	.XX° ± 1.0°						
.XXX ± 0.08	.XXX ± 0.5°	APPROVE	BY				
		SCALE	SHEET	UNIT			
		1:1	1/1	MM			
 							
		DRW NO:	REV: A				

