

Multi-Fiber Patch Cord, 12-fiber, OM4, LC/PC-LC/PC, 5 m, aqua

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Fiber distribution cable assembly

General Specifications

Color, boot A	Beige
Color, boot B	Beige
Color, connector A	Beige
Color, connector B	Beige
Connector A, quantity	12
Connector B, quantity	12
Interface, Connector A	LC/UPC
Interface, Connector B	LC/UPC
Jacket Color	Aqua
Total Fibers, quantity	12

Dimensions

Cord Length	5 m 16.404 ft
Diameter Over Jacket	6.4 mm 0.252 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum, connector A	0.15 dB
Insertion Loss, maximum, connector B	0.15 dB
Return Loss, minimum, connector A	35 dB
Return Loss, minimum, connector B	35 dB

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
---------------------	-------------------------------

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

