
**Part Number :** 2195620005
**Product Description :** EXTreme Guardian HD Right-Angle Plug Assembly with Guide Pins, 5 Power Circuits
**Series Number :** 219562
**Status :** Active
**Product Category :** Board-to-Board Connectors



## Documents and Resources

### Drawings

2195620005_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

2141130000-PS-000.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS | per |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

Downloaded from Arrow.com.

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Board-to-Board Connectors |
| Series | 219562 |
| Description | EXTreme Guardian HD Right-Angle Plug Assembly with Guide Pins, 5 Power Circuits |
| Application | Board-to-Board |
| Component Type | Plug |
| Product Name | EXTreme Guardian HD |
| UPC | 196823037160 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 130.0A |
| Voltage - Maximum | 125V |

### Physical

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 5 |
| Circuits (maximum) | 5 |
| Color - Resin | Black |
| Durability (mating cycles max) | 200 |
| First Mate / Last Break | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | Yes |
| Keying to Mating Part | No |
| Lock to Mating Part | No |
| Mated Height | 12.74mm |
| Material - Metal | High Conductivity Copper |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 23.962/g |
| Number of Rows | 1 |
| Orientation | Right Angle |
| Packaging Type | Tray |
| PCB Locator | Yes |
| PCB Retention | Yes |
| PCB Thickness - Recommended | 1.58mm |
| PC Tail Length | 3.30mm |
| Pitch - Mating Interface | 5.78mm |
| Plating min - Mating | 0.762µm |
| Plating min - Termination | 2.540µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| (p)ower-(s)ignal Configuration | 5p - 0s |
| Temperature Range - Operating | -40° to +125°C |
| Termination Interface Style | Through Hole - Compliant Pin |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| EXTreme Guardian HD Vertical Receptacle Assembly with Guide Receivers, 5 Power Circuits | 2195630005 |
| EXTreme Guardian HD Right-Angle Receptacle Assembly with | 2195640005 |

Downloaded from Arrow.com.

| Guide Receivers, 5 Power Circuits | |
|---|---|

This document was generated on Aug 01, 2026

Downloaded from Arrow.com.