



Part Number : [191980007](#)

Product Description : Avikrimp Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5)

Series Number : 19198

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : AA-835-10T



Documents and Resources

Drawings

[191980007_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19198
Description	Avikrimp Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5)
Keyword	Spade Terminal, Spade Terminals
Product Name	Avikrimp
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800753045996

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Flammability	94V-0
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	0.786/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Insulation Diameter	3.60mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.25-1.50

Application Tooling

Global

Description	Part Number
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	<u>638851300</u>

This document was generated on Apr 11, 2026