363RS6

Wall mounted socket

2CMA167498R1000



Surface socket-outlet, earthing sleeve position 6h, rated current 63A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA167498R1000
Function	Surface socket outlet
EAN	73926966749
Catalog Description	Surface socket-outlet, 6h, 63A, IP44, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421223
E-Number Norway	2416513
E-Number Sweden	E2416513
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TRS
Color	Red
Number of Poles	4
Clock Position	6Hour
Rated Current	63 ampere
Rated Voltage	380 ... 415 volt
Frequency	50 hertz|60 hertz
Degree of Protection	IP44
Cable Cross-Section	6...25 mm²
Housing Material	Thermoplastic (PBT)
Plug Angle	
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	107 millimetre
Product Net Height	254 millimetre
Product Net Length	254 millimetre
Product Net Depth	254 millimetre
Product Net Weight	0.99 kilogram

PACKAGING

Package Width	152 millimetre
Package Height	265 millimetre
Package Gross Weight	1.077 kilogram
Package Length	120 millimetre
Package Units	box 1 piece

Downloaded from Arrow.com.