



**Part Number :** [1300950146](#)

**Product Description :** Light Duty Wire Mesh Pulling Grip, Single Weave, Flexible Rope Eye, Short Mesh Length 0.305m (12.00"), Approximate Break Strength 1542.21kg (3400 lbs)

**Series Number :** 130095

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 35901



---

## Documents and Resources


### Drawings

[1300950146\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Cable Grips
Series	130095
Description	Light Duty Wire Mesh Pulling Grip, Single Weave, Flexible Rope Eye, Short Mesh Length 0.305m (12.00"), Approximate Break Strength 1542.21kg (3400 lbs)
Product Name	Light Duty
Type	Pulling Grip
UPC	78678835901

#### Agency

CSA	LR32159
-----	---------

#### Physical

Approximate Break Strength	1542.21kg (3400 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	12.70-15.49mm (.500-.610")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.305m (12.00")
Net Weight	72.968/g
Number of Holes	N/A
O-Ring	N/A

Thread Size	N/A
-------------	-----

---

This document was generated on May 21, 2026