



+ CONNECTORS

SCREENED



✓ Active

↓ **PRODUCT DRAWING**
English

TE CONNECTIVITY (TE)
TX15AZ00-1608

TX15AZ00-1608
TE Internal Number: CW0606-000

[Not EU RoHS or ELV Compliant](#)
[Find Compliant Alternatives](#)

Adapter Angle **00**

Cable Diameter Range **64 – 102 mm [25 – 4 in]**

Adapter Entry Size **08**

TE Adapter Code **15**

Material **Aluminum**

Product Drawings

[Tinel-Lock Backshell](#)
PDF
English

Catalog Pages/Data Sheets

[5-1654025-5_sec6_Adapters](#)
PDF
English

Product Specifications

Product Specification

[General Harness Repair Manual](#)
PDF
English

[General Information Package For Tinel-Lock Adapters](#)
PDF
English

[Adapter Finish Specifications](#)
PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Adapter Angle	00
	Style	Tinel-Lock
	Termination Device Type	Side-Entry Tinel-Lock Ring, Tinel-Lock Ring
	Connector Shell Size	24, 28

Body Features	Adapter Entry Size	08
	TE Adapter Code	15
	Material	Aluminum
	Adapter Plating Material	ZnNi per ASTM B841 over Suitable Underplated & Chromate
Dimensions	Cable Diameter Range	64 – 102 mm [25 – 4 in]
Industry Standards	Connector Detail Specification Number	AS31001, AS31011, AS31061, AS31071, AS31081
Other	Connector General Specification Number	AS50151 Solder Contact with ENDBELL
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	