

Technical data sheet

Article number:
114-01879

T18R



Product Group	Cable Ties for temperatures up to + 150 °C in Polyamide 4.6
Product Family	T-Series in PA46
Material	Polyamide 4.6 (PA46)
Colour	Natural (NA)
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	22.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Height (H)	3.7 mm
Length (L)	100 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +130 °C
Package Content	1000 pcs.
Package Content packed in	pcs.
Releasable Closure (Yes/No)	No
Specifications	ANSI/UL 62275, CSA -C22.2 no. 62275
Thickness (T)	1.0 mm
Toothing (Serration)	Inside Serrated
UL-File Number	E85319
UV-Stabilised	No
Variant	Inside Serrated
Weight/Unit	0.000315 kg
Width (W)	2.5 mm

