



+ TERMINALS & SPLICES  
CRIMP RINGS & SPADES



✓ Active

TE CONNECTIVITY (TE)  
TERMINAL,SOLIS R 16-14 3/8  
SOLISTRAND

2-34126-2  
TE Internal Number: 2-34126-2  
Mil-Spec: M7928/7-10

EU RoHS Compliant  
EU ELV Compliant  
Terminal Type Ring Tongue  
Stud Diameter 9.53 mm [ .375 in ]  
Sealed No  
Heavy Duty No  
Wire Size (AWG) 16

↓ PRODUCT DRAWING  
English

↓ 3D PDF

DOCUMENTATION

Product Drawings  
TERMINAL, RING TONGUE, SOLISTRAND  
PDF  
English

CAD Files  
Customer View Model  
2D\_DXF.ZIP  
English

3D PDF  
PDF  
3D

Customer View Model

3D\_IGS.ZIP

English

Customer View Model

3D\_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Sealed No
- Barrel Type Closed Barrel
- Wire/Cable Type Regular Wire
- Insulated No
- Insulated Wire Support No
- Stud Size 3/8
- Wire/Cable Composition Solid or Stranded
- Shape Code RING-048

Configuration Features

- Number of Holes 1

Body Features

- Plating Material Copper, Tin
- Inspection Slot No
- Plating Thickness (µin) 100
- Weight per Piece (g) 1.362

Contact Features

- Terminal Type Ring Tongue
- Terminal Orientation Straight
- Military Part Class Class II

Dimensions

- Stud Diameter 9.53 mm [ .375 in ]
- Wire Size (AWG) 16
- Wire Size (mm²) 1.25 – 2
- Wire Size (CMA) 2050 – 5180
- Barrel Inside Diameter 2.16 mm [ .085 in ]
- Material Thickness .84 mm [ .033 in ]
- Overall Length 25.27 mm [ .995 in ]
- Barrel Inside Diameter (Min) 2.16 mm [ .085 in ]

Usage Conditions

- Operating Temperature Range (°C) 170

Operation/Application

Heavy Duty No

Industry Standards

Government Qualified Yes

Packaging Features

Packaging Method Tape Mounted

Packaging Quantity 5000

Statement of Compliance

Statement of Compliance

PDF