

5

4





3

2



1

Hood lower part


Hood upper part



Strain relief 1



Strain relief 2



Flathead screws

				Det.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub hoods 09 poles not shielded	Maßstab/ Scale 1:1
			Detail.	27/02/03	SH			
			Insp.					
EC01696	19/04/10	SC	Stand.			 HARTING EURL F-95972 Paris	TB 09 67 009 0571	Blatt/ Page 1 / 1
34793	11/01/08	PK						
31392	27/02/03	SH						
Mod.	Det.	Name					Sub.	