



# Full Cycle Ratchet Crimper, #22-10 AWG Uninsulated (bare) Terminals and Splices

By Burndy  
Catalog # [MR20](#)

Full Cycle Ratchet Crimper, #22-10 AWG Bare.

### Features

- Permanent die sets
- Heavy duty forged steel frame
- Full cycle ratchet mechanism
- Emergency release
- Comfort grip handles

### Application

Crimping

### General

Application - For Use On	Uninsulated Terminals and Splices
Catalog Number	MR20
Die Type	Permanent Die Grooves
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
UPC	781810011195
UPC 14 Digit GTIN	00781810011195

### Dimensions

Dimensions	8.88 in x 6.00 in x 2.50 in
Height	2.5 in

Length	8.88 in
Weight	1.1 lb
Width	6 in

### Conductor Related

Crimping Ranges	#22 - #10 AWG
-----------------	---------------

### Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Package Contents	Tool only

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section N - Tooling](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Installation Manuals - MR15 MR18, MR20 Operating Manual](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_082\\_OTXF\\_MR15\\_MR18\\_MR20\\_lineart](#)
- [Sales Drawings - 10113613](#)
- [Specifications - MR20](#)



A Hubbell brand