








DETACHED LISTS			RoHS Compliant			
	TOLERANCES EXCEPT AS NOTED					
	MM .0 ± 0.25 .00 ± 0.20 .000 ± 0.10	± ± ±	TITLE			
	ANGLES ± 0.5		W/LIGHT PIPES			
			SFP 2 BY 6 CAGE+CONNECTOR_P			
THIRD ANGLE PROJECTION		DFTD Jack DATE 3/10/09'	DRAWING NO. CSFP0-3010-L /PART NO. SFP0-3010-L		SIZE A3	REV 0
SCALE : 2:1		DO NOT SCALE DRAWING			SHEET 1	OF 4







BEZEL CUT-OUT CENTER SPACING DETAIL
BEZEL THICKNESS: 0.8-2.6



DETACHED LISTS	MM (INCH)		RoHS Compliant				
	TOLERANCES EXCEPT AS NOTED		TITLE				
	MM		W/LIGHT PIPES				
	.0 ± 0.25	±	SFP 2 BY 6 CAGE+CONNECTOR_P				
	.00 ± 0.20	±					
	.000 ± 0.10	±					
	ANGLES ± 0.5						
		DFTD Jack		DRAWING NO. CSFP0-3010-L		SIZE	REV
THIRD ANGLE PROJECTION		DATE 3/10/09'		/PART NO. SFP0-3010-L		A3	0
		SCALE : 2:1		DO NOT SCALE DRAWING		SHEET 2 OF 4	



DETACHED LISTS	MM (INCH)		RoHS Compliant		 A TECHNITROL COMPANY		
	TOLERANCES EXCEPT AS NOTED		TITLE				
	MM		W/LIGHT PIPES				
	.0 ± 0.25	±	SFP 2 BY 6 CAGE+CONNECTOR_P				
	.00 ± 0.20	±					
	.000 ± 0.10	±					
	ANGLES ± 0.5						
				DFTD Jack		DRAWING NO. CSFP0-3010-L	SIZE
THIRD ANGLE PROJECTION		DATE 3/10/09'		/PART NO. SFP0-3010-L		A3	0
		SCALE : 2:1		DO NOT SCALE DRAWING		SHEET 3	OF 4



DETACHED LISTS	MM (INCH)		RoHS Compliant		 Pulse A TECHNITROL COMPANY			
	TOLERANCES EXCEPT AS NOTED		TITLE					
	MM	±					W/LIGHT PIPES	
	.0 ± 0.25	±						
	.00 ± 0.20	±	SFP 2 BY 6 CAGE+CONNECTOR_P					
	.000 ± 0.10	±						
	ANGLES ± 0.5		DFTD Jack		DRAWING NO. CSFP0-3010-L			
 THIRD ANGLE PROJECTION		DATE 3/10/09'		/PART NO. SFP0-3010-L				
		SCALE : 2:1		DO NOT SCALE DRAWING				
		SHEET 4		OF 4				
		SIZE A3		REV 0				