
Part Number : 1210120127
Product Description : mPm DIN Base, Form C-Micro 9.4mm, B39 Base, 3 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket with Screws
Series Number : 121012
Status : Active
Product Category : Circular Industrial Connectors
Engineering Part Number : B393000N0



Documents and Resources

Drawings

1210120127_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

PK-121012-B39-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121012
Description	mPm DIN Base, Form C-Micro 9.4mm, B39 Base, 3 Pole Plus Ground Terminal, 250V AC/300V DC, Black, Nitrile Gasket with Screws
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	883906361099

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	250V AC / 300V DC

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No

Downloaded from Arrow.com.

Form	C - Micro 9.4mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Tin
Net Weight	2.721/g
Orientation	Straight
Pitch - Mating Interface	9.40mm
Poles	3
Temperature Range - Operating	-40° to +90°C
Wire Size (AWG)	N/A

Downloaded from Arrow.com.