








P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	28AUG2023	NK	JDB
	F1	DRAWING RE-CREATED IN CRED	26DEC2023	NK	JDB



3D VIEW
SCALE 2:1



INSPECTION LEVEL 1: CONTROL CHART REQUIRED
 (1) PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS
 CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
(72) PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

⑦ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

1. COPLANARITY OF ALL CONTACTS AND CLIPS $\leq 0.1\text{mm}$

2 PART; 100 PCS. IN BUBBLE BAGS/BULK

 2				
1	-	-	TOP COVER	6
1	-	-	TRAY PACKAGING	5
1	1	-	SOLDER CLIP LEFT	4
1	1	-	SOLDER CLIP RIGHT	3
4	4	-	PINS	2
1	1	-	HOUSING	1
454829-E	254188-E	REV	DESCRIPTION	ITEM NO.
-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY		PARTS LIST		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N K NIKHIL 18AUG2023 CHK M SZELAG 20AUG2023 APVD J DE BRUIN 20AUG2023		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mk ISO 8015		NAME M12 MALE, A CODE, 4P, 17MM SMT	
		PRODUCT SPEC 108-94887		-	
MATERIAL - -		FINISH -		RESTRICTED TO -	
		WEIGHT -		SIZE A2	
		APPLICATION SPEC 114-94781		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C=254188-E	
				SCALE 5:1	
				SHEET 1 of 1	
				REV F1	