



Part Number : [1300850374](#)

Product Description : Woodhead POW-R-MATIC
Heavy Duty Cable Reel with Retraction Weight of 7lbs.,
12/4 SOW, 42.67m (140.0') Cord Length with Flying
Leads

Series Number : 130085

Status : Active

Product Category : Electrical Reels

Engineering Number : 92743



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Electrical Reels
Series	130085
Description	Woodhead POW-R-MATIC Heavy Duty Cable Reel with Retraction Weight of 7lbs., 12/4 SOW, 42.67m (140.0') Cord Length with Flying Leads
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 3R
NEMA Configuration	N/A
Product Name	POW-R-MATIC
Type	Cable Reel
UPC	78678879355

Agency

CSA	LR29921
-----	---------

Electrical

Current - Maximum per Contact	14.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	600V

Physical

Bulb Included	N/A
Cable Length	N/A
Cable Movement	Ratchet Lock
Cord Length	42.67m (140.0')
Cord Type	12/4 SOW
Depth	0.58m (22.750")

Drum Lock	Ratchet
Duty	Heavy
Guide Arm	Option Available
Height	0.59m (23.38")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Steel
Mounting Style	Rigid
Number of Conductors	4
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	3.2kg (7.0 lb)
Width	527.10mm (20.75")
Wire Size (AWG)	12

This document was generated on Sep 24, 2025