





NOTE -
 1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX DIA ON 1.000 ± .002 CENTERS
 2 - SUITABLE ONLY FOR APPLICATIONS IMPARTING A
 RAPID STROKE TO THE SWITCH PLUNGER

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	
OPERATING FORCE	4 1/2 OZ MAX
RELEASE FORCE	3/4 OZ MIN
DIFFERENTIAL TRAVEL	.015-.075
OVERTRAVEL	.156 MIN

ELECTRICAL DATA	
CONTACT ARRANGEMENT (SEE CIRCUIT DIAGRAM)	
UNDERWRITERS' LAB. INC. LISTED RATING	
15 A-125, 250, OR 480 VAC	
1 A-125 VDC; 0.5 A-250 VDC	
1/4 HP-125 VAC; 1/2 HP-250 VAC	

SCALE FULL	
DO NOT SCALE PRINT	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	
TOLERANCES ARE:	
ONE PLACE	(.0) ± .030
TWO PLACE	(.00) ± .015
THREE PLACE	(.000) ± .005
ANGLES	±
WEIGHT	

FO-50378
 DRAWN
 GCH 21 DEC 62
 CHECK
 DAW 5 JAN 63
 CHECK
 ISSUE 8
 DRAWING NUMBER 8
 REPLACES
 BZ-2AW82T