



Home / Product





Temperature Compensated \_ DO-35




View Product Details

Purchasing Tools

View Material Compliance

View CAD Model

Notifications

View Product Change Notifications


DT-2776


This Product is Not Web Purchasable.  
Please contact us if you are interested in purchasing this product.


Contact Us

Contact Us to Purchase

Would you like to have more flexibility for your orders?  
Apply for a Microchip Business Account and have access to unique features.

Request a quote for your large-quantity needs

Schedule your orders, up to 3 years in advance

Buy now, pay later with a Microchip credit limit

Apply for a Business Account

- Alternative Products

+
- Associated Products

+
- Associated Tools

+
- Reference Designs

+
- Design Help

+

How Can We Help?

Contact our Client Support Team

Your Order Status

Your Quote Status

Get Help with Your Project

International Shipping Information

Return Policy

Terms and Conditions

Privacy Notice

Your Privacy Choices  

Frequently Asked Questions

Accessibility Menu

Getting Started

Watch Video on the Benefits of Shopping Direct

Why Purchase Direct from Microchip?

Let us Program Your Device

Create a New Account

Apply for a Business Account

About Us

Products and Documentation

Getting Started With Microchip Products

Product Research and Datasheets

Application Design Center

Cross Reference Tool

Conflict Minerals

Export Control Data

RoHS Information

Technical Product Support

Find an Authorized Design Partner






Stay Connected



We'd love to hear what you think

Give us feedback





Customer Service Phone Numbers

<b>Australia</b> 1 800 193 884	<b>Austria</b> 0 800 298 364	<b>Belgium</b> 0 800 78 586	<b>Bulgaria</b> 00800 210 0073	<b>Canada</b> 1 888 624 7435	<b>China</b> 400 820 5079
<b>Croatia</b> 0800 890 094	<b>Czech Republic</b> +420 800 012 055	<b>Denmark</b> 802 53233	<b>Estonia / Lithuania / Latvia</b> 8 800 3 31 17	<b>Finland</b> 0 800 917 739	<b>France</b> 0 800 900 990
<b>Germany</b> 0 800 180 0121	<b>Greece</b> +30 800 848 1206	<b>China – Hong Kong SAR</b> 400 820 5079	<b>Hungary</b> 06 801 099 86	<b>Iceland</b> +45 4450 2827	<b>India</b> 000 800 1009 343
<b>Ireland</b> 1 800 901 628	<b>Israel</b> 1 80 945 0151	<b>Italy</b> 800 786 648	<b>Japan</b> +632 8479 2850	<b>Latin America</b> 1 888 624 7435	<b>Moldavia</b> 0 800 61527
<b>Netherlands</b> 0 800 022 4021	<b>New Zealand</b> 0 800 480 421	<b>Norway</b> 800 690 17	<b>Philippines</b> 180011102092	<b>Poland</b> 00 800 112 47 69	<b>Portugal</b> 800 819 068
<b>Romania</b> 0 800 896 371	<b>Russia</b> 8 800 301 7156	<b>Slovakia</b> 0 800 606 095	<b>Slovenia</b> 0 800 81772	<b>South Africa</b> 0 800 981 024	<b>South Korea</b> 0 82 2 554 7200
<b>Spain</b> 900 808 071	<b>Sweden</b> 0200 99 0585	<b>Switzerland</b> 0 800 848 253	<b>Taiwan</b> 00 801 127 676	<b>Turkey</b> 00 800 1420 30262	<b>United Kingdom</b> 800 032 3850
<b>United States</b> 1 888 624 7435	<b>ASEAN countries not listed</b> +632 8479 2850	<b>European countries not listed</b> +44 20 4602 9229			