

Part Number : [1300980061](#)

Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male, Cable Diameter 7.93-9.53mm (.312-.375")

Series Number : 130098

Status : Active

Product Category : Cable Grips

Engineering Part Number : 5526



Documents and Resources

Drawings

[1300980061_sd.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|--------------|---|
| Status | Active |
| Category | Cable Grips |
| Series | 130098 |
| Description | MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, Straight Male, Cable Diameter 7.93-9.53mm (.312-.375") |
| NEMA Rating | NEMA 3R |
| Product Name | MAX-LOC |
| Type | Strain Relief Grip |
| UPC | 78678872118 |

Agency

| | |
|-----|---------|
| CSA | LR32159 |
| UL | E76954 |

Physical

| | |
|----------------------------|--------------------------|
| Approximate Break Strength | N/A |
| Bale Length | N/A |
| Body Style | Straight |
| Cable Diameter | 7.93-9.53mm (.312-.375") |
| Color - Grommet | Gray |
| Eye Type | N/A |
| Gender | Male |
| Material - Body | Nylon |
| Material - Grip | N/A |
| Mesh Length | N/A |
| Net Weight | 22.679/g |
| Number of Holes | 1 |

| | |
|-------------|----------|
| O-Ring | No |
| Thread Size | 1/2" NPT |

Mates With / Use With

Use with Part(s)

| Description | Part Number |
|---|-------------------|
| MAX-LOC Lock Nut 1/2" NPT | <u>1300990143</u> |
| MAX-LOC Gasket Sealing Ring, 1/2" NPT, Black | <u>1300990149</u> |
| MAX-LOC O-Ring, 1/2" NPT | <u>1301800314</u> |

This document was generated on Apr 28, 2026