

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

? Contact
? Contact Type = Junior - Power - Timer
? Receptacle
? Wire Range = 0.30 -1.00 ² [22-17] mm
[AWG]
? Insulation Diameter = 2.15 mm

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

List all Documents

? GET 0.64 Connector System = No

? Brand = AMP