



Have a Question?
Chat with a Product
Information Specialist

My Cart | My Part Lists | [Sign In/Register](#) | English (Change)

What can we help you find?



[Products](#) | [Industries](#) | [Resources](#) | [About TE](#) | [My Account](#) | [Innovation](#) | [Support Center](#)

[Home](#) > [Products](#) > [Terminals & Splices](#) > [Product Feature Selector](#) > Product Details

2177419-3 Product Details

[Share](#) [Print](#) [Email](#)



2177419-3

TE Internal Number: 2177419-3

Active

[View 3D PDF](#)

Micro-Power & Power Quadlok System

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Applies To Printed Circuit Board
- Connector
- Header
- Connector Style = Plug
- 32 Positions

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [None Available](#)

Catalog Pages/Data Sheets:

- [None Available](#)

Product Specifications:

- [None Available](#)

Application Specifications:

- [None Available](#)

Instruction Sheets:

- [None Available](#)

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- Connector Type = Header
- Termination Method to PC Board = Through Hole - Solder
- Sealed = No
- Product Series = MQS
- PCB Mount Alignment = With
- PCB Mount Alignment Type = Locating Post(s)
- Mount Angle = 90°
- Tab Width (mm [in]) = 0.5 [0.0197]
- Keyed = Yes

Electrical Characteristics:

- Shielded = No

Dimensions:

- PCB Tail Length (mm [in]) = 2.35 [0.093]

Body Features:

- Staggered Centerline = Without
- Material = LCP

Contact Features:

- Contact Type = Tab
- Contact Style = Nano MQS
- [Tab Contacts](#) = With
- [Tab Contact Size](#) = 0.5
- 2.5mm Pin Diameter Contacts = Without
- [Contact Finish](#) = Tin
- Contact Shape = Right Angle
- Contact Base Material = CuMg

Housing Features:

- Connector Style = Plug
- [Centerline, Matrix \(mm \[in\]\)](#) = 1.5 x 1.8 [.059 x .071]
- Header Color = Black
- Housing Material = LCP - GF30

Configuration Features:

- [Number of Positions](#) = 32
- Fiber Optic Contacts = Without
- GET 0.64 Connector System = No

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- Key ID = A

Environmental:

- Operating Temperature (°C [°F]) = -40 - +120 [-40 - +248]

Conditions for Usage:

- Applies To = Printed Circuit Board
- For Use With = Receptacle Housing

Packaging Features:

- [Packaging Method](#) = Tray
- Packaging Quantity = 1

Other:

- Brand = TE Connectivity

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

