HDMI/DVI/USB KVM Cable Kit, 15 ft. (4.57 m)

MODEL NUMBER: **P782-015-DH**







Connects your HDMI- or DVI-enabled computer to a Tripp Lite HDMI KVM switch up to 15 ft. away.

Description

The P782-015-DH HDMI/DVI/USB KVM Cable Kit connects your computer to an HDMI-enabled KVM switch. It includes a 15-foot (4.6-meter) USB A/B keyboard/mouse cable, a 15-foot HDMI monitor cable and an adapter for converting a DVI port to HDMI. Premium foil and braid shielding in the cables delivers reliable, error-free signal quality and protection from EMI/RFI interference. Integral strain relief ensures the cable and connectors last a long time. The adapter's molded gold-plated connectors and contacts ensure excellent conductivity.

Features

Connects Your Computer to a HDMI KVM Switch

- Includes 15-ft. (4.6 m) USB A/B cable, 15-ft. (4.6 m) HDMI cable and DVI-to-HDMI adapter

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded gold-plated connectors and contacts for optimal signal quality
- Integral strain relief for long life
- Flexible PVC jackets easy to install in tight spaces

Highlights

- Includes 15-ft. (4.57 m) USB A/B and HDMI cables
- Includes DVI-to-HDMI adapter
- Premium foil and braid shielding
- Integral strain relief
- Molded gold-plated connectors and contacts

System Requirements

- Computer with available USB port and available HDMI or DVI port
- HDMI KVM switch

Package Includes

- USB cable (A/B M/M), 15-ft. (4.57 m)
- HDMI cable (M/M), 15-ft. (4.57 m)
- DVI-D dual link to HDMI adapter (M/F)

Specifications

OVERVIEW	
UPC Code	037332199942
Accessory Type	Cable Kit
Technology	DVI; HDMI
Accessory Class	KVM Switch Accessories
CONNECTIONS	

Downloaded from Arrow.com.

Side A - Connector 1	HDMI (FEMALE); HDMI (MALE); USB B (MALE)
Side B - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK); HDMI (MALE); USB A (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	0.50 x 9.30 x 10.50
Shipping Dimensions (hwd / cm)	1.27 x 23.62 x 26.67
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.