

RAD-ISM-900-ANT-YAGI-6.5-25-AS

Discontinued item

Order No.: 2867827



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2867827>

Panel antenna with surge protection, adapter cable MCX->N and assembly material, IP65 protection, gain 8.5 dBi, cable length 7.6 m, connection N (female)

Commercial data

GTIN (EAN)	 4 017918 976675
Note	Made-to-order
sales group	H179
Pack	1 pcs.
Customs tariff	85177019
Catalog page information	Page 677 (IF-2011)

Product notes

WEEE/RoHS-compliant since:
12/31/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Frequency range	900 MHz
Horizontal beamwidth	100 °
Vertical beamwidth	62 °

Impedance	50 Ω
Gain	8.5 dBi
Connection method	N (female) with cable (7.5 m)
Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 80 °C
Width	6 cm
Height	17 cm

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2012 Phoenix Contact
Technical modifications reserved;