








PCB layout, component side



Z (5:1)



Max. Temperature: 260°C during 10 seconds.
Find further technical information on DS 09550200302

0955 429 6822 333	2	4-40 UNC	Black insulator	Samples
0955 429 3821 741	1	M3	Black insulator	Reel packing: 140 connectors
0955 429 3822 741	1	4-40 UNC		
0955 429 6821 741	2	M3		
0955 429 6822 741	2	4-40 UNC		
0955 429 7821 741	3	M3		
0955 429 7822 741	3	4-40 UNC		
Part number	PL	Nut	Index designation	

	All Dimensions in mm Original Size DIN A3	Scale 2:1	Free size tol.		Ref.
	All rights reserved Department EL PD	Created by ZHUANGJ	Inspected by LUOK	Standardisation HOFFMANN	Sub.
HARTING Electronics GmbH D-32339 Espelkamp	Title D-Sub str SMT 37-pole male with screwlock & ground pad				Doc-Key / ECM-Nr. 100236629/UGD/001/C 500000139800
	Type TB	Number 0955429X82X			Rev. C Page 1/1